

PRODUCTS:

1. BIG F PRO 156 SANIC

2. BIG F PRO 256 SANIC

2. BIG F PRO 267 SANIC





PERFORMANCE DATA SHEET

MANUFACTURER

Name: ATLAS FILTRI SRL Address: Via Pierobon 32 - Limena, 35010, PD Phone Number: +39 049769055 **SELLER: Name:** Atlas FILTRI S.r.I. distributors

PRODUCTS

- BIG F PRO 156 SANIC
- BIG F PRO 256 SANIC
- BIG F PRO 267 SANIC

SUBSTANCES REDUCTION

The Atlas Filtri models listed above have been tested and certified under AS/NZS 4020 and AS 3497 and relevant NSF Standard listed in Clause 1.2 for reduction of Sediment. The performance of these products has been verified and substantiated as the test data summarized below indicates. These substances may not be in your water.

CLAIM TYPE	TREATMENT TYPE	PLAIN LANGUAGE DESCRIPTION	CONFORMANCE TO NSF STANDARDS AND PROTOCOLS	CATEGORY
Verified	Turbidity and particulate removal	Reduce Cloudiness	NSF/ANSI 42	III

Substance	NHMRC ADWG or USEPA SDWA MCL	Average Influent Concentration	Maximum Effluent Concentration	Minimum Percent removal	Average Effluent Concentration	Average percent removal
Sediments	-	10924 particles/ml	372 particles/ml	> 96.62 %	349 particles/ml	> 96.81 %

MCL - Maximum Contaminant level

Mg/I - milligrams per litre

Testing conditions:

• Flow rate was controlled at 4 gpm

Temperature 20 +/- 3 degree C

• pH 7,5 +/- 0,05

Refer to your owner's guide for more specific product and warranty information and to avoid contamination from improper handling and installation. Performance will vary on local water conditions. The substances reduced by this product are not necessarily in your water.

USE GUIDELINE

- Minimum Operating pressure 50 kPa
- Maximum operating pressure 830 kPa
- Do not Allow exposure to temperature below 4 °C
- Maximum operating temperature 40°C
- Nominal Flow rate:

BIG F PRO 156	SANIC	15,1 L/min
BIG F PRO 256	SANIC	15,1 L/min
BIG F PRO 267	SANIC	15,1 L/min

ELECTRICAL REQUIREMENTS

- Power supply: AC 110-240 V; 50/60 Hz
- UV lamp power: model 156: 56 W model 256: 56 W model 267: 67 W

• Total consumption: model 156: 61 W model 256: 61 W model 267: 73 W

• This system has to be installed according to local plumbing codes on the cold water line

• Replacement cartridges

BIG F PRO 156	SANIC	cartridge CPP 10" BIG SANIC 25 mcr - CPP 10" BIG SANIC 1 mcr
BIG F PRO 256	SANIC	cartridge CPP 20" BIG SANIC 25 mcr - CPP 20" BIG SANIC 1 mcr
BIG F PRO 267	SANIC	cartridge CPP 20" BIG SANIC 25 mcr - CPP 20" BIG SANIC 1 mcr

• This system requires regular replacement of the filter cartridge to maintain proper operation. Varying Sediment or organic substances levels may affect replacement frequency.

• Be sure to change the filter cartridge at least every six months; Or whenever you detect a change in taste or odour or decrease in flow.



CAUTION - Do not use with water that is microbiologically unsafe or of unknow quality without adequate disinfection before or after the system. Systems certified for CYST reduction may be used on disinfected water that may contain filterable CYSTS.

Buyer's Signature	Date	Seller's Signature	Date
			•••••











ATLAS FILTRI S.r.I. | via Pierobon, 32 | 35010 Limena, Italy Tel. +39.049.76.90.55 | Fax +39.049.76.99.94 | www.atlasfiltri.com